


Axial kit
EAMM-A-N80-72GA
Part number: 8063612



Data sheet

Feature	Value
Nominal length	70 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	151 kgmm ²
Transferable torque	47 Nm
Product weight	1263 g
Interface code, actuator	N80
Interface code, motor in	72GA
Note on materials	RoHS-compliant