


Vacuum generator OVEM-20-H-C-QO-CE-N-1PD

Part number: 8070095

FESTO



Data sheet

Feature	Value
Nominal width of Laval nozzle	2 mm
Width dimension	36 mm
Muffler construction type	Open
Mounting position	Any
Ejector characteristics	High vacuum Standard
Grade of filtration	40 µm
Manual override	Non-detenting Additionally via operating buttons
Integrated function	Ejector pulse valve, electric Flow control Shut off valve, electric Compressed air filter Air saving function, electrical Non-return valve Pneumatic muffler open Vacuum switch
Structural design	Modular
Short-circuit protection	yes
Measured variable	Relative pressure
Measuring principle	Piezoresistive
Switching element function	N/C contact N/O contact
Switching function	Window comparator Threshold value comparator
Valve function	Closed
Reverse polarity protection	for all electrical connections
Switching input to standard	IEC 61131-2
Display type	4-character alphanumeric Back-lit LCD
Display range	-0.999 bar...0 bar
Displayable unit(s)	bar
Setting options	Via display and pushbuttons
Switching position indication	LCD
Switching status indication	Optical

Feature	Value
Operating pressure	2 bar...8 bar
Operating pressure for max. vacuum	4 bar
Max. vacuum	93 %
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	98 l/min
Air supply time at nominal operating pressure	0.2 s
DC operating voltage range	20.4 V...27.6 V
Duty cycle	100%
Inductive protective circuit	Adapted to MZ, MY and ME coils
Max. output current	100 mA
Residual current	0.1 mA
Switching output	PNP
Voltage drop	2 V
Coil characteristics	24 V DC: low-current phase 0.3 W, high-current phase 2.55 W
Overload protection	Available
Certification	RCM compliance mark c UL us - Listed (OL)
KC characters	KC EMC
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Temperature of medium	0 °C...50 °C
Relative air humidity	5 - 85 %
Noise level at nominal operating pressure	62 dB(A)
Degree of protection	IP65
Ambient temperature	0 °C...50 °C
Max. tightening torque	0.8 Nm with internal thread 2.5 Nm with through-hole
Product weight	825 g
Pressure measuring range	-1 bar...0 bar
Accuracy in ± % FS	3 %FS
Input switching logic	PNP (positive switching)
Electrical connection	5-pin M12x1 Plug
Protection against tampering	PIN code
Type of mounting	With through-hole With internal thread With accessories
Pneumatic connection 1	QS-10
Pneumatic connection 3	Pneumatic muffler
Vacuum connection	QS-12
Note on materials	RoHS-compliant
Seals material	HNBR NBR
Female nozzle material	POM
Compressed air filter material	Fabric PA Sintered steel
Material of filter housing	PA-reinforced
Housing material	Wrought aluminum alloy PA-reinforced
Material of adjusting screw	Steel

Feature	Value
Muffler material	Wrought aluminum alloy POM PU foam
Material of screws	Steel
Material of plug housing	Brass, nickel-plated
Material of pins	Steel
Material of jet nozzle	Wrought aluminum alloy
Material of pneumatic fitting	Brass, nickel-plated