


Round cylinder CRDSNU-B-40-160-PPS-A-MG-A1

Part number: 8073982

FESTO



Data sheet

Feature	Value
Stroke	160 mm
Piston diameter	40 mm
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
For use in the food industry	See supplementary material information
Ambient temperature	0 °C...80 °C
Theoretical force at 6 bar, retracting	633 N
Theoretical force at 6 bar, advancing	754 N
Moving mass at 0 mm stroke	232 g
Additional moving mass per 10 mm stroke	15.8 g
Basic weight with 0 mm stroke	1327 g
Additional weight per 10 mm stroke	23.8 g
Type of mounting	With accessories
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Cover material	High-alloy stainless steel
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel