


Diffuse scan SOOE-BS-L-PNLK-T

Part number: 8075670

FESTO



Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E232949
Note on materials	RoHS-compliant
Measuring principle	Optoelectronic
Detection method	Reflection light sensor with HGA
Type of light	Laser Red
Max. light spot	1 mm for scan width of 200 mm
Minimum object diameter	2 mm
Working range	7 mm...300 mm
Ambient temperature	-40 °C...60 °C
Max. black-white difference	45 %
Reference material	Standard white 90%, 100x100 mm
Switching output	Push-pull
Switching element function	Switchable PNP, bright-switching NPN, dark-switching
Hysteresis	18 mm
Max. switching frequency	1650 Hz
Max. output current	100 mA
Voltage drop	0 V...1.5 V
Timer function	Via IO-Link®
Short-circuit protection	Pulsed
Protocol	IO-Link®
IO-Link®, protocol version	Device V 1.1
IO-Link®, profile	Smart sensor profile

Feature	Value
IO-Link®, function classes	Process data variable (PDV) Identification Diagnostics Teach channel Switching signal channel (SSC)
IO-Link®, communication mode	COM2 (38,4 kBd)
IO-Link®, SIO mode support	Yes
IO-Link®, port class	A
IO-Link®, process data width OUT	2 bit
IO-Link®, process data content OUT	1 bit (emitter disable) 1 bit (hold)
IO-Link®, process data width IN	1 bit
IO-Link®, process data content IN	1 bit SSC (switching signal)
IO-Link®, minimum cycle time	2.3 ms
IO-Link®, data memory required	2 KB
DC operating voltage range	10 V...30 V
Residual ripple	10 %
Idle current	25 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw-type lock
Material of pin contacts	Brass, gold-plated
Type of mounting	With through-hole for M3 screw
Tightening torque	0.8 Nm
Mounting position	Any
Product weight	10 g
Housing material	PC PMMA
Ready status indication	LED green
Switching status indication	LED yellow
Setting options	IO-Link® Potentiometer Teach-in
Setting range, lower limit	25 mm
Setting range, upper limit	300 mm
Degree of protection	IP65 IP67 IP69K
Insulation voltage	500 V
Surge resistance	1 kV
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Laser safety class	1
Contamination level	3