


# Mini slide DGST-20-150-PA

Part number: 8085147

FESTO



## Data sheet

Feature	Value
Stroke	150 mm
Adjustable end-position range/front length	32.9 mm
Adjustable end-position range/rear length	31.1 mm
Piston diameter	20 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Twin piston Yoke Piston rod Slide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. speed	0.8 m/s
Repetition accuracy	<= 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Impact energy in the end positions	0.35 J
Cushioning length	1.2 mm
Max. force F <sub>y</sub>	1300 N
Max. force F <sub>z</sub>	1300 N
Max. torque M <sub>x</sub>	20 Nm
Max. torque M <sub>y</sub>	17 Nm
Max. torque M <sub>z</sub>	17 Nm

Feature	Value
Theoretical force at 6 bar, retracting	317 N
Theoretical force at 6 bar, advancing	377 N
Moving mass	1293.5 g
Product weight	2831 g
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel