

Mini slide DGST-20-10-E1A

Part number: 8078862

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 10 mm |
| Piston diameter | 20 mm |
| Drive unit operating mode | Yoke |
| Cushioning | Elastomer cushioning, at both ends, stroke not adjustable |
| Mounting position | Any |
| Guide | Ball bearing cage guide |
| Structural design | Twin piston Yoke Piston rod Slide |
| Position sensing | For proximity sensor |
| Operating pressure | 0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi |
| Max. speed | 0.5 m/s |
| Repetition accuracy | <= 0.3 mm |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | -10 °C...60 °C |
| Impact energy in the end positions | 0.2 J |
| Cushioning length | 1 mm |
| Max. force Fy | 1600 N |
| Max. force Fz | 1600 N |
| Max. torque Mx | 16 Nm |
| Max. torque My | 18 Nm |
| Max. torque Mz | 18 Nm |
| Theoretical force at 6 bar, retracting | 317 N |
| Theoretical force at 6 bar, advancing | 377 N |

| Feature | Value |
|----------------------|----------------------------------|
| Moving mass | 440 g |
| Product weight | 978 g |
| Type of mounting | With through-hole |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | HNBR |
| Guide material | POM TPE-E High-alloy steel |
| Housing material | Wrought aluminum alloy |
| Piston rod material | High-alloy stainless steel |