

Mini slide DGST-8-20-PA

Part number: 8085111

FESTO



Data sheet

Feature	Value
Stroke	20 mm
Adjustable end-position range/front length	16.3 mm
Adjustable end-position range/rear length	14.4 mm
Piston diameter	8 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Twin piston Yoke Piston rod Slide
Position sensing	For proximity sensor
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar 21.75 psi...116 psi
Max. speed	0.8 m/s
Repetition accuracy	<= 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Impact energy in the end positions	0.05 J
Cushioning length	1.5 mm
Max. force F _y	275 N
Max. force F _z	275 N
Max. torque M _x	2 Nm
Max. torque M _y	2 Nm
Max. torque M _z	2 Nm

Feature	Value
Theoretical force at 6 bar, retracting	45 N
Theoretical force at 6 bar, advancing	60 N
Moving mass	88.4 g
Product weight	170.8 g
Type of mounting	With through-hole
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel