


Mini slide DGST-25-40-PA

Part number: 8085152

FESTO



Data sheet

Feature	Value
Stroke	40 mm
Adjustable end-position range/front length	40.2 mm
Adjustable end-position range/rear length	40.2 mm
Piston diameter	25 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Twin piston Yoke Piston rod Slide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. speed	0.8 m/s
Repetition accuracy	<= 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Impact energy in the end positions	0.45 J
Cushioning length	1.2 mm
Max. force F _y	1310 N
Max. force F _z	1310 N
Max. torque M _x	13 Nm
Max. torque M _y	12 Nm
Max. torque M _z	12 Nm

Feature	Value
Theoretical force at 6 bar, retracting	495 N
Theoretical force at 6 bar, advancing	589 N
Moving mass	1013.5 g
Product weight	2016 g
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Guide material	POM TPE-E High-alloy steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel