


Parallel kit
EAMM-U-38-V25-35A-63
Part number: 8093286

FESTO



Data sheet

Feature	Value
Size	38
Center-to-center distance	63 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	3600 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Mass moment of inertia	4.35 kgmm ²
No-load driving torque	0.05 Nm
Transferable torque	0.5 Nm
Product weight	218 g
Interface code, actuator	V25
Interface code, motor in	35A 23AB
Note on materials	RoHS-compliant