

Push-in Y-connector NPQR-Y-Q16-E

Part number: 8085728

FESTO



Data sheet

Feature	Value
Size	Standard
Tubing insertion depth	23.5 mm
Mounting position	Any
Design	Y-shape
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Information on operating pressure	Water: max. 0.7 MPa at 0 - 80 °C
Certificate issuing authority	NSF C0556009
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1
For use in the food industry	See declaration of conformity NSF/ANSI 169
Ambient temperature	-5 °C...150 °C
Note on ambient temperature	with PUN-H: -20°C - 60°C
Product weight	140.9 g
Pneumatic connection 1	for pneumatic tubing outside diameter 16 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 16 mm
Note on materials	RoHS-compliant
Housing material	High-alloy stainless steel
Guard ring material	High-alloy stainless steel
Releasing ring material	High-alloy stainless steel
Material of tubing seal	FPM

Feature	Value
Material of tube retaining claw	High-alloy stainless steel
Thrust ring material	PPSU