


Sub-base VABS-P16-10S-M5

Part number: 8097804

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width | 26 mm |
| Mounting position | Any |
| Special features | Oxygen-compatible as per DIN EN 1797 |
| Max. no. of valve positions | 1 |
| Operating pressure | 0 bar...7 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [6:3:4] Inert gas Air Oxygen Nitrogen |
| Information on operating and pilot media | Operation with oil lubrication not possible Maximum particle size 5 µm |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -20 °C...70 °C |
| Temperature of medium | -10 °C...60 °C |
| Relative air humidity | 0 - 60 % Non-condensing |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 25 g |
| Type of mounting | With through-hole With internal thread |
| Pneumatic connection 1 | M5 |
| Pneumatic connection 2 | M5 |
| Note on materials | RoHS-compliant |
| Material of sub-base | Wrought aluminum alloy |