

Solenoid coil VACC-S13-18-K4-3U-EX4ME

Part number: 8109398

FESTO



Data sheet

| Feature | Value |
|---|--|
| Actuation type | Electrical |
| Mounting position | Any |
| Switching position indication | no |
| Duty cycle | 100% |
| Insulation class | H |
| Coil characteristics | 230 V DC: 1.8 W 230 V AC: 40/65 Hz, power 1.8 VA |
| Permissible voltage fluctuations | -15 % / +10 % |
| CE marking (see declaration of conformity) | as per EU explosion protection directive (ATEX) As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | as per UK EX instructions (UK-X) as per UK RoHS instructions (UK-R) |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Db (IEC-EX) EPL Gb (GB) EPL Gb (IEC-EX) |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 1 (IEC-EX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (IEC-EX) Zone 21 (UKEX) Zone 22 (ATEX) |
| Certificate issuing authority | IECEx BVS 15.0075X German Technical Control Board (TÜV) 21 UKEX 7015 X |
| ATEX category gas | II 2G |
| ATEX category for dust | II 2D |
| Type of ignition protection for gas | Ex eb mb IIC T* Gb |
| Type of (ignition) protection for dust | Ex tb IIIC T°C Db |
| Explosive ambient temperature | T4/T130°C: -30°C ≤ Ta ≤ +60°C T5/T95°C: -30°C ≤ Ta ≤ +60°C T6/T85°C: -30°C ≤ Ta ≤ +50°C |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Degree of protection | IP65 |
| Product weight | 330 g |

| Feature | Value |
|-----------------------|--|
| Electrical connection | Terminal box, cable entry thread M20x1.5 |
| Note on materials | RoHS-compliant |