


Twin cylinder DGTZ-GF-6- -P-A

Part number: 8116420

FESTO



Data sheet

Feature	Value
Min. stroke limit (hard)	51 mm
Stroke	51 mm...60 mm
Max. stroke limit (hard)	60 mm
Adjustable end position range/length	10 mm
Piston diameter	6 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Position sensing	For proximity sensor
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Impact energy in the end positions	0.01 Nm
Max. payload as a function of the stroke at defined distance xs	0.5 N...0.6 N
Theoretical force at 6 bar, retracting	18.6 N
Theoretical force at 6 bar, advancing	34 N
Moving mass	25 g...27 g
Moving mass at 0 mm stroke	15 g
Additional moving mass per 10 mm stroke	2 g
Product weight	148 g...164 g
Basic weight with 0 mm stroke	65.5 g
Additional weight per 10 mm stroke	16.5 g
Pneumatic connection	M5

Feature	Value
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel