

# Parallel gripper DHPC-6-A-NC-S-2

Part number: 8116749

**FESTO**



## Data sheet

Feature	Value
Size	6
Stroke per gripper jaw	2 mm
Max. interchangeability	0.2 mm
Max. gripper jaw angular play ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.02 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Single-acting Closed
Gripper function	Parallel
Gripping force backup	During closing
Structural design	Connection direction at side Flat mounting type for gripper fingers Lever Positively driven motion sequence
Guide	Ball guide
Position sensing	For proximity sensor
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Operating pressure	0.35 MPa...0.8 MPa 3.5 bar...8 bar 50.75 psi...116 psi
Max. operating frequency of pneumatic gripper	3 Hz
Min. opening time at 6 bar	16 ms
Min. closing time at 6 bar	16 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L

Feature	Value
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-10 °C...60 °C
Gripping force per gripper jaw at 6 bar, opening	10.4 N 5.2 N
Mass moment of inertia	0.012 kgcm <sup>2</sup>
Maximum force on gripper jaw F <sub>z</sub> , static	22 N
Maximum torque on gripper jaw, M <sub>x</sub> static	0.24 Nm
Maximum torque on gripper jaw, M <sub>y</sub> static	0.11 Nm
Maximum torque on gripper jaw, M <sub>z</sub> static	0.11 Nm
Product weight	27 g
Type of mounting	Direct mounting via through-hole Direct fastening via thread Optionally:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Housing material	Aluminum, anodized
Gripper jaw material	High-alloy stainless steel