

# Twin cylinder DGTZ-GF-32-70-P-A

Part number: 8100663

**FESTO**



## Data sheet

Feature	Value
Stroke	70 mm
Adjustable end position range/length	10 mm
Piston diameter	32 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Impact energy in the end positions	0.4 Nm
Max. payload as a function of the stroke at defined distance xs	15.6 N
Theoretical force at 6 bar, retracting	724 N
Theoretical force at 6 bar, advancing	966 N
Moving mass	1551 g
Product weight	1551 g
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel