

Parallel gripper DHPC-25-A-NC-S-2

Part number: 8116863

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 25 |
| Stroke per gripper jaw | 7 mm |
| Max. interchangeability | 0.2 mm |
| Max. gripper jaw angular play ax, ay | 0 deg |
| Max. gripper jaw backlash Sz | 0 mm |
| Rotational symmetry | 0.2 mm |
| Pneumatic gripper repetition accuracy | 0.02 mm |
| Number of gripper jaws | 2 |
| Actuator system | Pneumatic |
| Mounting position | Any |
| Mode of operation | Single-acting Closed |
| Gripper function | Parallel |
| Gripping force backup | During closing |
| Structural design | Connection direction at side Flat mounting type for gripper fingers Lever Positively driven motion sequence |
| Guide | Ball guide |
| Position sensing | For proximity sensor |
| Operating pressure | 0.25 MPa...0.8 MPa 2.5 bar...8 bar 36.25 psi...116 psi |
| Max. operating frequency of pneumatic gripper | 3 Hz |
| Min. opening time at 6 bar | 114 ms |
| Min. closing time at 6 bar | 49 ms |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C...60 °C |
| Gripping force per gripper jaw at 6 bar, opening | 291.4 N 145.7 N |

| Feature | Value |
|--|--|
| Mass moment of inertia | 1.59 kgcm ² |
| Maximum force on gripper jaw Fz, static | 155.9 N |
| Maximum torque on gripper jaw, Mx static | 4.83 Nm |
| Maximum torque on gripper jaw, My static | 2.52 Nm |
| Maximum torque on gripper jaw, Mz static | 2.52 Nm |
| Product weight | 438 g |
| Type of mounting | Direct mounting via through-hole Direct fastening via thread On mounting frame With through-hole and dowel pin With internal thread and dowel pin Optionally: |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Housing material | Aluminum, anodized |
| Gripper jaw material | High-alloy stainless steel |