

# Adapter kit DADG-AK-F9-2

Part number: 8104804

**FESTO**



## Data sheet

Feature	Value
Size	2
Based on norm	VDI/VDE 3847-2
Mounting position	Any
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar 29 psi...116 psi
Nominal operating pressure	0.6 MPa 6 bar 87 psi
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Dew point min. 10 °C below the ambient temperature and temperature of medium Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-20 °C...80 °C
Product weight	418 g
Note on materials	RoHS-compliant
Adapter material	High-alloy stainless steel
Adapter plate material	Wrought aluminum alloy, anodized
Seals material	NBR
Material of screws	High-alloy stainless steel