

# Radial gripper DHRC-20-A-S-NO

Part number: 8128698

FESTO



## Data sheet

Feature	Value
Size	20
Max. interchangeability	0.2 mm
Max. opening angle	180 deg
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.1 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Single-acting Open
Gripper function	Radial
Gripping force backup	On opening
Structural design	Connection direction at side Positively driven motion sequence
Position sensing	For proximity sensor
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar 21.75 psi...116 psi
Max. operating frequency of pneumatic gripper	2 Hz
Min. opening time at 6 bar	73 ms
Min. closing time at 6 bar	32 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Total gripping torque at 6 bar, closing	112 Ncm
Mass moment of inertia	0.294 kgcm <sup>2</sup>
Maximum force on gripper jaw Fz, static	100 N
Maximum torque on gripper jaw, Mx static	4 Nm
Maximum torque on gripper jaw, My static	2 Nm
Maximum torque on gripper jaw, Mz static	4 Nm

Feature	Value
Product weight	220 g
Type of mounting	Direct mounting via through-hole Direct fastening via thread With through-hole and dowel pin With internal thread and dowel pin Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover cap material	Wrought aluminum alloy, anodized
Housing material	Wrought aluminum alloy, anodized
Gripper jaw material	High-alloy steel