


End plate CPX-AP-A-EPLI

Part number: 8129250

FESTO



Data sheet

Feature	Value
Dimensions W x L x H	(installation dimensions) 48.4 mm x 117.2 mm x 57.5 mm
Width dimension	50.1 mm
Type of mounting	Direct mounting via through-hole On H-rail with accessories On mounting frame with through-hole for M5 screw with through-hole for M6 screw
Product weight	245 g
Mounting position	Arbitrary, on H-rail: horizontal
Ambient temperature	-20 °C...50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95 % Non-condensing
Nominal altitude of use above sea level	<= 2000 m ASL (> 79.5 kPa)
Max. installation height	3500 m
Information on max. installation height	> 2000 m ASL (< 79.5 kPa) Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class (CRC)	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms as per EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 as per FN 942017-5 and EN 60068-2-27
Protection class	III
Contamination level	2
Overvoltage category	II

Feature	Value
Max. cable length	50 m system communication
LABS (PWIS) conformity	VDMA24364-B2-L
Material fire test	UL94 V-0 (housing)
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Housing material	Die-cast aluminum, coated
Cover material	PBT-reinforced
Material of screws	Steel, nickel-plated Steel, galvanized
Seals material	PU foam
O-ring material	FPM
Diagnostics via LED	Diagnostics per module Power supply for electronics/sensors Load power supply
Diagnose per internal communication	Load switch-off Communication error Short circuit/overload Power OUT PL Short circuit/overload Power OUT PS Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
Max. address capacity inputs	2048 byte
Max. address capacity outputs	2048 byte
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	M8x1, D-coded as per EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP
Communication interface, shielding	yes
Voltage forwarding, function	Outgoing electronics/sensors and load
Voltage forwarding, connection type	Socket
Voltage forwarding, connection technology	M8x1, A-coded as per EN 61076-2-104
Voltage forwarding, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Note on nominal operating voltage DC	Protected Extra-Low-Voltage as per IEC 60204-1
Nominal operating voltage DC load	24 V
Permissible voltage fluctuations load	± 25 %
Nominal operating voltage DC for electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25 %
Intrinsic current consumption at nominal operating voltage for electronics/sensors	typically 45 mA
Intrinsic current consumption at nominal operating voltage load	typically 11 mA
Power failure buffering	10 ms
Potential separation between the supply voltages electronics/sensor technology and load/valves	yes
Reverse polarity protection	yes
Behavior after end of overload of the sensor supply	No automatic return with overload at Power-OUT
Behavior after end of overload of the outputs	No automatic return with overload at Power-OUT
Fuse protection (short circuit)	yes, Power-Out PS+PL