

Angle gripper DHC-10-A-S-NO

Part number: 8133476

FESTO



Data sheet

Feature	Value
Size	10
Max. interchangeability	0.2 mm
Max. opening angle	30 deg
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.1 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Single-acting Open
Gripper function	Angle
Gripping force backup	On opening
Structural design	Connection direction at side Positively driven motion sequence
Position sensing	For proximity sensor
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar 29 psi...116 psi
Max. operating frequency of pneumatic gripper	3 Hz
Min. opening time at 6 bar	6 ms
Min. closing time at 6 bar	12 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Total gripping torque at 6 bar, closing	15.9 Ncm
Mass moment of inertia	0.039 kgcm ²
Maximum force on gripper jaw F _z , static	40 N
Maximum torque on gripper jaw, M _x static	0.4 Nm
Maximum torque on gripper jaw, M _y static	0.5 Nm
Maximum torque on gripper jaw, M _z static	0.5 Nm

Feature	Value
Product weight	53.5 g
Type of mounting	Direct mounting via through-hole Direct fastening via thread With through-hole and dowel pin With internal thread and dowel pin Optionally:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Cover cap material	Wrought aluminum alloy, anodized
Housing material	Wrought aluminum alloy, anodized
Gripper jaw material	High-alloy steel