


Twin cylinder DGTZ-GF-32- -P-A

Part number: 8116424

FESTO



Data sheet

Feature	Value
Min. stroke limit (hard)	101 mm
Stroke	101 mm...200 mm
Max. stroke limit (hard)	200 mm
Adjustable end position range/length	10 mm
Piston diameter	32 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Impact energy in the end positions	0.4 Nm
Max. payload as a function of the stroke at defined distance xs	3 N...10.8 N
Theoretical force at 6 bar, retracting	724 N
Theoretical force at 6 bar, advancing	966 N
Moving mass	740 g...1051 g
Moving mass at 0 mm stroke	421 g
Additional moving mass per 10 mm stroke	31.5 g
Product weight	1809 g...2636 g
Basic weight with 0 mm stroke	966 g
Additional weight per 10 mm stroke	83.5 g
Pneumatic connection	G1/8

Feature	Value
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel