


# Parallel gripper DHPC-40-A-NC-S-1

Part number: 8116904

**FESTO**



## Data sheet

Feature	Value
Size	40
Stroke per gripper jaw	15 mm
Max. interchangeability	0.2 mm
Max. gripper jaw angular play ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.02 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Single-acting Closed
Gripper function	Parallel
Gripping force backup	During closing
Structural design	Connection direction at side Lever Side mounting type for gripper fingers Positively driven motion sequence
Guide	Ball guide
Position sensing	For proximity sensor
Operating pressure	0.25 MPa...0.8 MPa 2.5 bar...8 bar 36.25 psi...116 psi
Max. operating frequency of pneumatic gripper	1 Hz
Min. opening time at 6 bar	370 ms
Min. closing time at 6 bar	78 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Gripping force per gripper jaw at 6 bar, opening	733.5 N 366.8 N

Feature	Value
Mass moment of inertia	15.31 kgcm <sup>2</sup>
Maximum force on gripper jaw Fz, static	351.5 N
Maximum torque on gripper jaw, Mx static	16.15 Nm
Maximum torque on gripper jaw, My static	9.55 Nm
Maximum torque on gripper jaw, Mz static	9.55 Nm
Product weight	1469 g
Type of mounting	Direct mounting via through-hole Direct fastening via thread On mounting frame With through-hole and dowel pin With internal thread and dowel pin Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Housing material	Aluminum, anodized
Gripper jaw material	High-alloy stainless steel