

# Adapter kit EHAM-MA-L9-90-L2-80

Part number: 8128229



## Data sheet

| Feature                          | Value                       |
|----------------------------------|-----------------------------|
| Size                             | 90                          |
| Mounting position                | Any                         |
| Structural design                | Standard design             |
| Corrosion resistance class (CRC) | 0 - No corrosion stress     |
| LABS (PWIS) conformity           | VDMA24364-B2-L              |
| Ambient temperature              | -10 °C...80 °C              |
| Product weight                   | 1215 g                      |
| Type of mounting                 | With through-hole and screw |
| Interface code, base             | L9-90                       |
| Interface code, layout           | L2-80                       |
| Note on materials                | RoHS-compliant              |
| Adapter plate material           | Aluminum, anodized          |
| Material of screws               | Steel, nickel-plated        |
| Material of centering elements   | High-alloy steel            |