

Limit switch box SRBC-CA4-YR90-N-1-P-C2

Part number: 8137097

FESTO



Data sheet

Feature	Value
Certification	RCM compliance mark c CSA us (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC characters	KC EMC
Note on materials	RoHS-compliant
Safety integrity level (SIL)	SIL 2
Measuring principle	Inductive
Ambient temperature	-20 °C...80 °C
Switching output	PNP
Switching element function	N/O contact
Max. switching frequency	1000 Hz
Max. output current DC	100 mA
Voltage drop	3 V
Residual current	0 mA...0.5 mA
Short-circuit protection	Pulsed
DC operating voltage range	10 V...30 V
Idle current	15 mA
Reverse polarity protection	for all electrical connections
Microswitch type	P&F NBB2-V3-E2
Electrical connection	Screw terminal
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Spring-loaded terminal
Electrical connection 1, number of pins/wires	10
Closable nominal conductor cross-section	0.25 mm²...2.5 mm²
Approved cable diameter	5 mm...13 mm
Dimensions W x L x H	127 mm x 98 mm x 122 mm
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1 VDI/VDE 3845 size AA 2 VDI/VDE 3845 size AA 3

Feature	Value
Mounting position	Any
Product weight	800 g
Housing colour	Gray
Housing material	Die-cast aluminum
Seals material	NBR
Shaft material	High-alloy stainless steel
Material of screws	High-alloy stainless steel
Material of mounting bracket	High-alloy stainless steel
Circlip material	High-alloy stainless steel
Disc material	High-alloy stainless steel
Cover cap material	PC
Position indicator	Yellow/red
Angle detection setting range	0 deg...90 deg
Storage temperature	-20 °C...50 °C
Degree of protection	IP67 NEMA 4/4X
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Contamination level	3