

**Pneumatic valve**  
**VOGI-F100FS-T32H-M-F90**  
Part number: 8141660

**FESTO**



**Data sheet**

Feature	Value
Structural design	Sub base valve Pilot-controlled piston poppet valve
Actuation type	Pneumatic
Sealing principle	Soft
Mounting position	Any
Type of mounting	With accessories
Valve function	4/2, monostable Fail safe
Mode of operation	Double-acting
Operating pressure	0.33 MPa...0.8 MPa 3.3 bar...8 bar 47.85 psi...116 psi
Reset method	Mechanical spring
Pneumatic connection	Sub-base design, airing
Pneumatic connection 1	G1/2
Operating medium	Compressed air as per ISO 8573-1:2010 [7:7:-] Inert gas
Information on operating and pilot media	Operation with oil lubrication not possible
Temperature of medium	-20 °C...80 °C
Ambient temperature	-20 °C...80 °C
Standard nominal flow rate	1093 l/min
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Smooth-anodized wrought aluminum alloy (20 µm)
Cover material	Smooth-anodized wrought aluminum alloy (20 µm)
Seals material	EPDM NBR
Material of screws	High-alloy stainless steel
Material of spring	Spring steel
Product weight	880 g
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)

Feature	Value
Corrosion resistance class (CRC)	3 - High corrosion stress