

Sub-base VABP-C13-100HFT0-F90-VDE1E

Part number: 8141661

FESTO



Data sheet

| Feature | Value |
|--|--|
| Mounting position | Any |
| Structural design | 1001 channel structure |
| Valve connection conforms to standard | VDI/VDE 3847-1 |
| Operating pressure | 0 MPa...0.8 MPa 0 bar...8 bar |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:7:-] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Temperature of medium | -40 °C...80 °C |
| Ambient temperature | -40 °C...80 °C |
| Product weight | 1300 g |
| Type of mounting | With accessories |
| Pneumatic connection | Sub-base design, airing |
| Note on materials | RoHS-compliant |
| Cover material | Smooth-anodized wrought aluminum alloy (20 µm) |
| Seals material | EPDM NBR |
| Housing material | Smooth-anodized wrought aluminum alloy (20 µm) |
| Material of screws | High-alloy stainless steel |