


# Standards-based cylinder CRDSNU-20-10-P-A

Part number: 8152557

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 10 mm  |
| Piston diameter                          | 20 mm  |
| Piston rod thread                        | M8   |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Conforms to standard                     | ISO 6432   |
| Piston rod end                           | External thread  |
| Structural design                        | Piston<br>Piston rod<br>Cylinder barrel                            |
| Position sensing                         | For proximity sensor   |
| Operating pressure                       | 0.1 MPa...1 MPa<br>1 bar...10 bar                                  |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 3 - High corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Cleanroom class                          | Class 6 according to ISO 14644-1                                   |
| For use in the food industry             | See declaration of conformity                                      |
| Ambient temperature                      | -20 °C...80 °C   |
| Impact energy in the end positions       | 0.2 J  |
| Theoretical force at 6 bar, retracting   | 158 N  |
| Theoretical force at 6 bar, advancing    | 188 N  |
| Moving mass at 0 mm stroke               | 42 g   |
| Additional moving mass per 10 mm stroke  | 4 g  |
| Basic weight with 0 mm stroke            | 310 g  |
| Additional weight per 10 mm stroke       | 7 g  |
| Type of mounting                         | With accessories   |
| Pneumatic connection                     | G1/8   |
| Note on materials                        | RoHS-compliant   |
| Cover material                           | High-alloy stainless steel   |

| Feature                     | Value                      |
|-----------------------------|----------------------------|
| Piston rod material         | High-alloy stainless steel |
| Material of cylinder barrel | High-alloy stainless steel |