


Stepper motor EMMT-ST-42-S-R

Part number: 8156161

FESTO



Data sheet

Feature	Value
Ambient temperature	0 °C...40 °C
Note on ambient temperature	up to 80°C with derating -2%/°C
Max. installation height	4000 m
Information on max. installation height	with 1,000 m and longer only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90 % Non-condensing
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	B
Max. winding temperature	130 °C
Rating class according to EN 60034-1	S1
Motor type as per EN 60034-7	IM B5 IM V1 IM V3
Mounting position	Any
Degree of protection	IP40
Note on degree of protection	IP40 for motor shaft without rotary shaft seal IP65 for motor housing, incl. connection technology
Interface code, motor out	42A
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connection technology	M17x0.75
Electrical connection 1, number of pins/wires	12
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Certification	RCM compliance mark c UL us - Recognized (OL)

Feature	Value
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E342973
Nominal operating voltage DC	48 V
Number of pole pairs	50
Motor holding torque	250 Nm
Peak torque	250 Nm
Max. rotational speed	2700 rpm
Max. mechanical speed	9000 rpm
Step angle with full step	1.8 deg
Step angle tolerance	±5%
Continuous stall current	2 A
Motor nominal current	1800 A
Peak current	2 A
Motor constants	133 Nm/A
Voltage constant, phase	12100 mVmin
Phase winding resistance	2100 Ohm
Winding inductance phase	3 mH
Winding longitudinal inductivity Ld (phase)	1600 mH
Cross inductivity Lq (phase)	3 mH
Electric time constant	1400 ms
Thermal time constant	22 min
Thermal resistance	3500 K/W
Measuring flange	200 x 200 x 15 mm, steel
Total output inertia moment	0.035 kgcm ²
Product weight	370 g
Permissible axial shaft load	10 N
Permissible radial shaft load	28 N