


Compact cylinder ADN-S-50-10-A-P-A-F1A

Part number: 8142908

FESTO



Data sheet

| Feature | Value |
|--|---|
| Stroke | 10 mm |
| Piston diameter | 50 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Piston rod end | External thread |
| Structural design | Piston Piston rod |
| Position sensing | For proximity sensor |
| Variants | Recommended for production facilities for the manufacture of lithium-ion batteries Piston rod at one end |
| Operating pressure | 0.04 MPa...1 MPa 0.4 bar...10 bar 5.8 psi...145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | 0 °C...60 °C |
| Impact energy in the end positions | 1 J |
| Theoretical force at 6 bar, retracting | 1057 N |
| Theoretical force at 6 bar, advancing | 1178 N |
| Moving mass at 0 mm stroke | 104 g |
| Additional moving mass per 10 mm stroke | 16 g |
| Basic weight with 0 mm stroke | 324 g |
| Additional weight per 10 mm stroke | 63 g |

| Feature | Value |
|---------------------------|---|
| Type of mounting | With through-hole With internal thread |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy, anodized |
| Material of dynamic seals | TPE-U(PU) |
| Housing material | Wrought aluminum alloy, anodized |
| Piston rod material | High-alloy stainless steel |