


Parallel gripper HPPF-16-16-A-S

Part number: 8143712

FESTO



Data sheet

Feature	Value
Size	16
Complete stroke	16 mm
Stroke per gripper jaw	8 mm
Max. gripper jaw angular play ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Pneumatic gripper repetition accuracy	0.06 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Double-acting
Cushioning	Elastic cushioning rings/pads at both ends
Gripper function	Parallel
Gripping force backup	Without
Structural design	Flat mounting type for gripper fingers Gear rack/pinion Positively driven motion sequence
Guide	Ball guide
Position sensing	For proximity sensor
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Operating pressure	0.1 MPa...0.7 MPa 1 bar...7 bar 14.5 psi...101.5 psi
Max. operating frequency of pneumatic gripper	1 Hz
Min. opening time at 6 bar	55 ms
Min. closing time at 6 bar	47 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III

Feature	Value
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Gripping force per gripper jaw at 6 bar, opening	218.2 N 109.1 N
Gripping force per gripper jaw at 6 bar, closing	218.2 N 109.1 N
Maximum force on gripper jaw Fz, static	180 N
Max. torque Mx	4.4 Nm
Max. torque My	2.2 Nm
Max. torque Mz	2.2 Nm
Product weight	415 g
Type of mounting	Direct mounting via through-hole Direct fastening via thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover cap material	Wrought aluminum alloy, anodized
Cover material	Wrought aluminum alloy, anodized
End plate material	High-alloy stainless steel
Housing material	Wrought aluminum alloy, anodized
Gripper jaw material	High-alloy steel
Piston seal material	TPE-U(PU)
O-ring material	NBR
Material of screws	Steel, coated
Gear rack material	High-alloy stainless steel