

Standards-based cylinder CRDSNU-12-50-P-A

Part number: 8152527

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 50 mm |
| Piston diameter | 12 mm |
| Piston rod thread | M6 |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Conforms to standard | ISO 6432 |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | For proximity sensor |
| Operating pressure | 0.1 MPa...1 MPa 1 bar...10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| For use in the food industry | See declaration of conformity |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in the end positions | 0.07 J |
| Theoretical force at 6 bar, retracting | 51 N |
| Theoretical force at 6 bar, advancing | 68 N |
| Moving mass at 0 mm stroke | 19 g |
| Additional moving mass per 10 mm stroke | 2 g |
| Basic weight with 0 mm stroke | 101 g |
| Additional weight per 10 mm stroke | 4 g |
| Type of mounting | With accessories |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Cover material | High-alloy stainless steel |

| Feature | Value |
|-----------------------------|----------------------------|
| Piston rod material | High-alloy stainless steel |
| Material of cylinder barrel | High-alloy stainless steel |