

Stepper motor EMMB-ST-42-L-SB

Part number: 8156134

FESTO



Data sheet

Feature	Value
Ambient temperature	-15 °C...40 °C
Note on ambient temperature	up to 80°C with derating -2%/°C
Max. installation height	4000 m
Information on max. installation height	with 1,000 m and longer only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90 % Non-condensing
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	B
Max. winding temperature	130 °C
Rating class according to EN 60034-1	S1
Motor type as per EN 60034-7	IM B5 IM V1 IM V3
Mounting position	Any
Degree of protection	IP20
Note on degree of protection	IP40 for motor shaft without rotary shaft seal
Interface code, motor out	42A
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connection technology	Connection diagram L5
Electrical connection 1, number of pins/wires	14
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Nominal operating voltage DC	48 V

Feature	Value
Number of pole pairs	50
Motor holding torque	630 Nm
Peak torque	630 Nm
Max. rotational speed	3200 rpm
Max. mechanical speed	9000 rpm
Step angle with full step	1.8 deg
Step angle tolerance	±5%
Continuous stall current	3700 A
Motor nominal current	2900 A
Peak current	4 A
Motor constants	162 Nm/A
Voltage constant, phase	10600 mVmin
Phase winding resistance	600 Ohm
Winding inductance phase	800 mH
Winding longitudinal inductivity Ld (phase)	1450 mH
Cross inductivity Lq (phase)	800 mH
Electric time constant	1300 ms
Thermal time constant	16 min
Thermal resistance	2400 K/W
Measuring flange	200 x 200 x 15 mm, steel
Total output inertia moment	0.088 kgcm ²
Product weight	700 g
Permissible axial shaft load	10 N
Permissible radial shaft load	28 N
Brake holding torque	630 Nm
Brake DC operating voltage	24 V
Brake current consumption	340 A
Brake power consumption	8200 W
Brake coil resistance	70900 Ohm
Brake coil inductivity	146 mH
Brake separation time	28 ms
Brake closing time	41 ms
DC brake response delay	8 ms
Max. brake no-load speed	9000 rpm
Max. brake friction work	1500 J
	1
Brake mass moment of inertia	0.006 kgcm ²
Switching cycles, holding brake	10 million idle actuations (without friction work!)