


# Shock absorber DYSD-Q11-7-5-Y1F-Y14

Part number: 8161522

FESTO



## Data sheet

| Feature                           | Value                         |
|-----------------------------------|-------------------------------|
| Size                              | 7                             |
| Stroke                            | 5 mm                          |
| Cushioning                        | Self-adjusting                |
| Mounting position                 | Any                           |
| Position sensing                  | None                          |
| Max. impact velocity              | 1 m/s                         |
| Reset time at room temperature    | 0.2 s                         |
| Mode of operation                 | Pushing<br>Single-acting      |
| Corrosion resistance class (CRC)  | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity            | VDMA24364-B2-L                |
| Ambient temperature               | 0 °C...60 °C                  |
| Cushioning length                 | 5 mm                          |
| Max. stop force                   | 300 N                         |
| Max. energy absorption per stroke | 4 J                           |
| Max. energy absorption per hour   | 12000 J                       |
| Max. residual energy              | 0.01 J                        |
| Resetting force                   | 12 N                          |
| Min. insertion force              | 40 N                          |
| Product weight                    | 20 g                          |
| Type of mounting                  | With lock nut                 |
| Note on materials                 | RoHS-compliant                |
| Seals material                    | NBR                           |
| Housing material                  | High-alloy steel              |
| Piston rod material               | High-alloy steel              |
| Nut material                      | Steel, galvanized             |