


Stop kit DADP-SP-G9-20-F

Part number: 8173539

FESTO



Data sheet

| Feature | Value |
|----------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Size | 20 |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-C1-L |
| Suitability for the production of Li-ion batteries | Product corresponds to Festo's internal product definition for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | -10 °C...60 °C |
| Max. stop force | 300 N |
| Max. tightening torque | 2 Nm |
| Tightening torque tolerance | ± 15 % |
| Product weight | 87 g |
| Type of mounting | Direct fastening via thread |
| Note on materials | RoHS-compliant |
| Stops material | High-alloy steel |
| Material of screws | Steel |