


Axial kit
EAMM-A-D40-60P-S1-G2
Part number: 8197497



Data sheet

Feature	Value
Nominal length	52 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	12.5 Nm
Product weight	340 g
Interface code, actuator	D40
Interface code, motor in	60P 60PA
Note on materials	RoHS-compliant