

**Axial kit**  
**EAMM-A-L38-70GA-G2**  
Part number: 8199483



**Data sheet**

| Feature                  | Value               |
|--------------------------|---------------------|
| Nominal length           | 42.5 mm             |
| Mounting position        | Any                 |
| Max. rotational speed    | 8000 rpm            |
| LABS (PWIS) conformity   | VDMA24364-B2-L      |
| Storage temperature      | -25 °C...60 °C      |
| Relative air humidity    | 0 - 95 %            |
| Degree of protection     | IP40                |
| Ambient temperature      | -10 °C...60 °C      |
| Mass moment of inertia   | 4 kgmm <sup>2</sup> |
| Transferable torque      | 4.4 Nm              |
| Product weight           | 598 g               |
| Interface code, actuator | L38                 |
| Interface code, motor in | 70GA                |
| Note on materials        | RoHS-compliant      |