

Sub-base
VABS-K2-10S-16-M5-P
Part number: 8186875

FESTO



Data sheet

Feature	Value
Size	10
Nominal width	1.6 mm
Valve size	10 mm
Fluid connector	Internal thread M5
Mounting position	Any
Structural design	Connection direction at side
Max. no. of valve positions	1
Flow direction	Non-reversible
Operating medium	Liquid media Gaseous media
Information on operating and pilot media	Observe resistance of materials that come into contact with media
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...70 °C
For use in the food industry	See supplementary material information
Temperature of medium	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Max. tightening torque for valve mounting	0.2 Nm
Max. tightening torque of pneumatic fitting	1 Nm
Max. tightening torque	0.6 Nm
Product weight	20 g
Sub-base mounting type	With through-hole
Pneumatic valve mounting type	With internal thread
Note on materials	RoHS-compliant
Material of sub-base	PEEK