


Manifold sub-base VABX-A-P-BU-12-SHUH-U

Part number: 8191788

FESTO



Data sheet

Feature	Value
Size	1 2
Width dimension	19.05 mm
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Integrated function	With electrical manifold module
Flow direction	Reversible
Compatible with	Valve terminal VTUX-A-P
Suitability for vacuum	yes
Dimensions W x L x H	19.05 mm x 104.3 mm x 43.1 mm
Contamination level	2
Certification	RCM compliance mark
KC characters	KC EMC
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95 %
Degree of protection	IP65
Ambient temperature	-5 °C...50 °C
Product weight	56.3 g
Electrical actuation	Multi-pin
Sub-base mounting type	With through-hole
Type of mounting	Tie rod
Pneumatic connection 1	For 15 mm cartridge
Pneumatic connection 5	For 15 mm cartridge
Note on materials	RoHS-compliant
Material of sub-base	PA-reinforced
Seals material	NBR
Clip material	High-alloy stainless steel