

Conector indicator MCL-230AC

Numar piesa: 10001

FESTO



Fisa de date

Caracteristica	Valoare
Greutate produs	12 g
Conector electric	Forma A Stecker conform DIN EN 175301-803
Tensiunea nominala de functionare CA	230 V
Frecventa retelei	50 Hz...60 Hz
Fluctuatii de tensiune admise	-20 % / +15 %
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	-20 °C...60 °C
Marca CE (consultati Declaratia de conformitate)	conform Directivei UE privind joasa tensiune
Marca UKCA (consultati Declaratia de conformitate)	conform reglementarilor UK privind echipamentele electrice
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	ranforsat cu PA6