


Quarter turn actuator DFPD-3500-SY-Y-90-RD-F16

Part number: 8211838

FESTO



Data sheet

Feature	Value
Size of valve actuator	3500
Flange hole pattern	F16
Swivel angle	90 deg
End-position adjusting range at 0°	-5 deg...5 deg
End-position adjusting range at nominal swivel angle	-5 deg...5 deg
Depth shaft connection	48 mm
Standard connection for valve	ISO 5211
Mounting position	Any
Mode of operation	Double-acting
Structural design	Scotch yoke system
Closing direction	Clockwise closing
Valve connection conforms to standard	VDI/VDE 3845 (NAMUR)
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 2
Safety function	The safety function consists of the drive switching to the defined safety switching position. This switching movement is achieved by pressurizing the corresponding pressure chamber with compressed air. The value of the torque generated depends on the pressure difference between the two pressure chambers separated by the piston.
Safety integrity level (SIL)	Up to SIL 2 low demand mode up to SIL 3 in a redundant architecture
Certified for safety function to ISO 13849 and IEC 61508 (SIL)	Product can be used in safety-related parts of control systems up to SIL 2, low demand up to SIL 3 in a redundant architecture
Burst pressure	16.14 bar
Operating pressure	0.3 MPa...0.54 MPa 3 bar...5.4 bar 43.5 psi...78.3 psi
Nominal operating pressure	0.538 MPa 5.38 bar 78.01 psi
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX)
UKCA marking (see declaration of conformity)	acc. to UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)

Feature	Value
Explosion prevention and protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
Certificate issuing authority	German Technical Control Board (TÜV) Rheinland 968/V 2959.00/2025
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex h IIC T6 Gb
Type of (ignition) protection for dust	Ex h IIIC T85°C Db
Explosive ambient temperature	-20°C ≤ Ta ≤ +80°C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:3:4]
Information on operating and pilot media	Dew point min. 10 °C below the ambient temperature and temperature of medium Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Ambient temperature	-20 °C...80 °C
Torque at nominal operating pressure and 0° swivel angle	3993.9 Nm
Torque at nominal operating pressure and 90° swivel angle	3993.9 Nm
Note about the torque	The actuator's operating torque must not be higher than the maximum permissible torque listed in ISO 5211, based on the size of the mounting flange and the coupling.
Air consumption at 6 bar per cycle 0°-nominal swivel angle-0°	183.4 l
Product weight	92000 g
Shaft connection	T46
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Material of end caps	Spheroidal graphite cast iron
Stop screw material	Steel
Seals material	NBR
Material of spring	Spring steel
Spring rod material	Steel
Housing material	Spherulitic graphite iron
Material of piston	Spheroidal graphite cast iron
Piston rod material	Steel
Tie rod material	Steel
Material of cylinder barrel	Steel