

Coupling hub
EAMC-H-35-13-GB16-19
Part number: 8228661



Data sheet

Feature	Value
Diameter of holder 1	19 mm
Size	30/35
Nominal length	23.4 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	5.8 kgmm ²
Transferable torque	15 Nm
Product weight	31 g
Note on materials	RoHS-compliant