

Ventil electromagnetic VZWF-L-M22C-N112-400-1P4-10-R1

Numar piesa: 1492172

FESTO



Fisa de date

Caracteristica	Valoare
Structura constructiva	Ventil cu membrana controla in forta
Tip de actionare	electric
Principiul de etansare	slab
Pozitie de instalare	Magnet, in picioare
Tipul de montare	Instalarea liniei
Conectare armatura	1 1/2 NPT
Conector electric	Forma A Stecker conform EN 175301-803 design patrat
Latimea nominala	40 mm
Functie de ventil	2/2 monostabil inchis
Actionare manuala	fara
Directia de curgere	nu este reversibil
Mediu	Aer comprimat conform ISO 8573-1:2010 [7:::] Gaze inerte Ulei mineral Apa lichide neutre alte medii de curgere, la cerere
Presiune nominala armatura PN	40
Diferenta de presiune	0 MPa 0 bar 0 psi
Caracteristici bobina	24 V CC: 30,0 W
Fluctuatii de tensiune admise	+/- 10 %
Presiune mediu	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi

Caracteristica	Valoare
Vascozitate max.	22 mm ² /s
Temperatura medie	-10 °C...80 °C
Temperatura ambianta	-10 °C...35 °C
Rata de scurgere in conformitate cu EN 12266-1	A
Debit Kv	22.5 m ³ /h
Debit nominal standard (normalizat conform DIN 1343)	23500 l/min
Timp de comutare pornit	620 ms
Timp de comutare oprit	1140 ms
Nota privind materialele	Conform RoHS
Conformitatea LABS	VDMA24364 zona III
Material carcasa	Otel inoxidabil turnat
Cod material carcasa	1.4581
Material garnituri	NBR
Material suruburi	otel inoxidabil inalt aliat
Numar material surub	1.4301
Greutate produs	4500 g
Marca CE (consultati Declaratia de conformitate)	conform Directivei UE privind echipamentele sub presiune
Tip de protectie	IP65
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune