

## Suport ventuza vacuum ESH-HB-2-PK

Numar piesa: 189206

**FESTO**



### Fisa de date

| Caracteristica                       | Valoare                                                               |
|--------------------------------------|-----------------------------------------------------------------------|
| Latimea nominala                     | 2 mm                                                                  |
| Volum                                | 0.188 cm <sup>3</sup>                                                 |
| Pozitie de instalare                 | orice                                                                 |
| Structura constructiva               | Racord de vacuum lateral                                              |
| Atribuirea suportului de ventuza     | Dimensiune 2                                                          |
| Mediu de operare                     | aer atmosferic conform ISO 8573-1:2010 [7:::]                         |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune                                          |
| Conformitatea LABS                   | VDMA24364-A1-L                                                        |
| Temperatura ambianta                 | -10 °C...60 °C                                                        |
| Greutate produs                      | 11 g                                                                  |
| Tipul de montare                     | cu filet interior                                                     |
| Fixarea ventuzei                     | Diametru 4 mm                                                         |
| Racord de vacuum                     | PK-4                                                                  |
| Nota privind materialele             | Conform RoHS                                                          |
| Material garnituri                   | NBR<br>Otel                                                           |
| Suport material                      | Aluminiu<br>Alama, nichelata<br>POM<br>Otel calit<br>Otel aliaj inalt |