


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-120-P-G3-SAS-140

Numar piesa: 552198

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	120 mm
Dimensiune flansa motor	140 mm
Joc de rasucire	0.12 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	3:1
Turatie de lucru max.	6500 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	115 Nm
Momentul de inertie al reductorului	2.63 kgcm ²
Cuplu de iesire max.	184 Nm
Randament max.	98 %
Rigiditate la torsiune	12 Nm/arcmin
Greutate produs	6000 g
Interfata de iesire la unitatea de actionare	120G
Interfata reductor unitate de actionare	140A
Nota privind materialele	Conform RoHS