



Placa de capat VMPAL-EPL-SD44

Numar piesa: 560939

FESTO



Fisa de date

Caracteristica	Valoare
Latime	43 mm
Lungime	107.3 mm
Numarul max. de pozitii de ventil	32
Ansamblu insula de ventile	Ventile cu dimensiuni cu posibilitate de combinare
Numar maxim de bobine de ventil	32
Presiune de lucru	-0.09 MPa...1 MPa -0.9 bar...10 bar
Presiunea de control	0.3 MPa...0.8 MPa 3 bar...8 bar
Tensiune nominala de functionare CC	24 V
Clasa de rezistenta la coroziune KBK	3 - stres intens de coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Tip de protectie	IP67
Nota privind tipul de protectie	in stare asamblata cu accesorii VMPAL-KM
Temperatura ambianta	-5 °C...50 °C
Greutate produs	190 g
Conector electric 1, functie	Multi-pin
Conexiune electrica 1, tip de conectare	Stecher
Conexiune electrica 1, tehnologie de conectare	Sub-D
Conexiune electrica 1, numar de pini/fire	44
Nota privind materialele	Conform RoHS
Material placa de capat	Aluminiu turnat sub presiune Ranforsat cu PA