

Manometru PAGN-63-0.025M-G14-1.6

Numar piesa: 8036756

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 MPa...0.025 MPa
Conform cu standardul	EN 837-1
Dimensiune nominala, manometru	63
Protectie la explozie	Respectati informatiile din certificat Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	Instalarea liniei
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...0.025 MPa 0 bar...0.25 bar 0 psi...3.625 psi
Factor de incarcare alternanta	0.66
Clasa de precizie de masurare	1,6
Tip de protectie	IP43
Temperatura de depozitare	-40 °C...70 °C
Temperatura medie	-20 °C...60 °C
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Partea din spate, centrat
Conexiune pneumatica	G1/4
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	ABS

Caracteristica	Valoare
Material vizor	PS
Culoarea carcasei	negru
Greutate produs	220 g
Scala	Scara dubla MPa (exterior) bar (interior)