


Angrenaj|cutie de viteze|reductor|transmisie EMGA-80-P-G20-EAS-80

Numar piesa: 8141743

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	80 mm
Dimensiune flansa motor	80 mm
Joc de rasucire	0.15 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	20:1
Turatie de lucru max.	7000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	120 Nm
Momentul de inertie al reductorului	0.406 kgcm ²
Cuplu de iesire max.	240 Nm
Randament max.	96 %
Rigiditate la torsiune	10.4 Nm/arcmin
Greutate produs	2500 g
Interfata de iesire la unitatea de actionare	80G
Interfata reductor unitate de actionare	80P
Nota privind materialele	Conform RoHS