


Angrenaj|cutie de viteze|reductor|transmisie EMGA-80-P-G8-SAS-100

Numar piesa: 8141750

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	80 mm
Dimensiune flansa motor	100 mm
Joc de rasucire	0.12 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	8:1
Turatie de lucru max.	7000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	50 Nm
Momentul de inertie al reductorului	0.37 kgcm ²
Cuplu de iesire max.	80 Nm
Randament max.	97 %
Rigiditate la torsiune	8.4 Nm/arcmin
Greutate produs	2300 g
Interfata de iesire la unitatea de actionare	80G
Interfata reductor unitate de actionare	100A
Nota privind materialele	Conform RoHS