




- For threaded connections
M5, G $\frac{1}{8}$... G $\frac{1}{2}$

- For tubing I.D.
3 ... 13 mm

- Aluminium or polymer design

- With sealing ring or moulded-on
sealing ring

Quick connectors CK/CX

Product range overview

FESTO

Design	Design	Type	Connection D1		Tubing I.D.	Free of copper, PTFE and silicone	→ Page
			M thread	G thread			
Straight	Quick connector – Female thread with sealing ring						
		ACK Metal type	–	G1/8	3, 4, 6		3 / 5.5-5
				G1/4	4, 6		
				G3/8	6, 9		
				G1/2	13		
	Quick connector – Male thread with sealing ring						
		CK Metal type	M5	–	3, 4		3 / 5.5-6
			–	G1/8	3, 4, 6		
				G1/4	4, 6, 9		
				G3/8	6, 9, 13		
				G1/2	13		
		CK-...-KU Polymer design	–	G1/8	3, 4, 6		3 / 5.5-6
				G1/4	4, 6, 9		
				G3/8	6, 9		
	Bulkhead quick connector – Female thread with sealing ring						
		QCK	M5	–	3		3 / 5.5-7
			–	G1/8	4		
				G1/4	6		
				G3/8	9		
	Bulkhead quick connector						
		SCK Metal type	–	–	3, 4, 6, 9		3 / 5.5-8
		SCK-...-KU Polymer design	–	–	3, 4, 6, 9		3 / 5.5-8
	End cap for plastic tube connectors and barbed connectors						
		CV-PK	–	–	3, 4, 6, 9	–	3 / 5.5-9

Quick connectors CK/CX

Product range overview

FESTO

Design	Design	Type	Connection D1			Tubing I.D.	Free of copper, PTFE and silicone	→ Page
			M thread	R thread	G thread			
L-shape	Elbow quick connector							
		GCK-...-KU	–	R1/8	–	4, 6	■	3 / 5.5-10
				R1/4		4, 6		
				R3/8		6, 9		
	Elbow quick connector, rotatable, with 2 sealing rings							
		LCK Metal type	M5	–	–	3, 4	■	3 / 5.5-11
			–		G1/8	3, 4, 6		
					G1/4	4, 6, 9		
					G3/8	6, 9, 13		
					G1/2	13		
		LCK-...-KU Polymer design	–	–	G1/8	4, 6	■	3 / 5.5-11
			G1/4	4, 6				
	Elbow quick connector with sealing ring (rotatable 360°)							
		LCKN	M5	–	–	3, 4	–	3 / 5.5-12
			–		G1/8	3, 4, 6		
					G1/4	4, 6		
					G3/8	6		
T-shape	T quick connector, rotatable, with 2 sealing rings							
		TCK Metal type	M5	–	–	3, 4	■	3 / 5.5-13
			–		G1/8	3, 4, 6		
					G1/4	4, 6		
					G3/8	6, 9		
					G1/2	13		
		TCK-...-KU Polymer design	–	–	G1/8	4, 6	■	3 / 5.5-13
			G1/4	4, 6				
	T-distributor							
		FCK-...-KU	–	–	–	3	■	3 / 5.5-14
					4			
					6			
					9			
	Locknut for CK tube connector							
		MCK Metal type	–	–	–	3, 4, 6, 9, 13	–	3 / 5.5-15
		MCK-...-KU Polymer design	–	–	–	3, 4, 6, 9	–	3 / 5.5-15

Quick connectors CK/CX

Product range overview

FESTO

Design	Design	Type	Connection D1		Tubing I.D.	Free of copper, PTFE and silicone	→ Page
			M thread	G thread			
Multiple distributor	Ring piece with 2 seals						
		LK Metal type	M5	–	3, 4	–	3 / 5.5-16
			–	G1/8	3, 4, 6		
				G1/4	4, 6		
				G3/8	6		
		LK-...-KU Polymer design	–	G1/8	4, 6	–	3 / 5.5-16
				G1/4	4, 6		
	Ring piece with 2 seals						
		TK Metal type	M5	–	3, 4	–	3 / 5.5-17
			–	G1/8	3, 4, 6		
				G1/4	4, 6		
				G3/8	6		
		TK-...-KU Polymer design	–	G1/8	4, 6	–	3 / 5.5-17
				G1/4	4, 6		
	Hollow bolt with 2 ring pieces						
		VT-...-2 2 ring pieces	M5	G1/8	3, 4, 6	–	3 / 5.5-18
				G1/4	4, 6		
				G3/8	6		
				VT-...-3 3 ring pieces	M5		
		G1/4	4, 6				
		G3/8	6				
For metal braided hoses PX							
Straight	Quick connector						
		ACX	–	G1/8	4	–	3 / 5.5-19
				G1/4	6		
				G3/8	9		
	Quick connector						
		CX	–	G1/8	4, 6	–	3 / 5.5-19
				G1/4	4, 6		
				G3/8	9		
	L-shape	Elbow quick connector					
		LCX	–	G1/8	4	–	3 / 5.5-20
				G1/4	6		
				G3/8	9		
T-shape	T quick connector						
		TCX	–	G1/8	4	–	3 / 5.5-20
				G1/4	6		
				G3/8	9		

Quick connectors ACK

Technical data

FESTO


Quick connector ACK

Female thread with sealing ring

Material:

Blue anodised aluminium

Free of copper, PTFE and silicone



Dimensions and ordering data									
Connection	Nominal size	Tubing I.D.	L1	L2	Ø1	Ø2	Part No.	Type	PU*
D1	[mm]								
G $\frac{1}{8}$	2.4	3	23.9	9	13	8	5 664	ACK- $\frac{1}{8}$ -PK-3	10
	3.4	4	27	9	13	12	3 714	ACK- $\frac{1}{8}$ -PK-4	10
	5.3	6	27	9	13	14	7 842	ACK- $\frac{1}{8}$ -PK-6	10
G $\frac{1}{4}$	3.4	4	30	12	17	12	3 713	ACK- $\frac{1}{4}$ -PK-4	10
	5.3	6	30	12	17	14	3 712	ACK- $\frac{1}{4}$ -PK-6	10
G $\frac{3}{8}$	5.3	6	31	12	19	14	3 711	ACK- $\frac{3}{8}$ -PK-6	10
	8	9	37.4	15	19	19	3 710	ACK- $\frac{3}{8}$ -PK-9	1
G $\frac{1}{2}$	12	13	40.2	15	27	24	4 099	ACK- $\frac{1}{2}$ -PK-13	1

* Packaging unit quantity

Quick connectors CK

Technical data

FESTO

Quick connector CK

Male thread with sealing ring

Material:

M thread: Steel, aluminium

G thread: Blue anodised aluminium

Free of copper, PTFE and silicone

Quick connector CK-...-KU

Male thread with moulded-on sealing ring


Material:

Polymer

Free of copper, PTFE and silicone

Pressure range: 0 ... 10 bar

Temperature range: -10 ... +60 °C



Dimensions and ordering data									
Connection D1	Nominal size [mm]	Tubing I.D.	L1	L2	≡	≡1	Part No.	Type	PU*
Metal design									
M5	2.0	3	19.5	4	7	8	3 561	CK-M5-PK-3	10
	2.9	4	21.7	4	10	–	3 562	CK-M5-PK-4	10
G1/8	2.0	3	21.6	5	13	8	3 563	CK-1/8-PK-3	10
	2.9	4	24.7	5	13	12	2 027	CK-1/8-PK-4	10
	4.9	6	24.8	5	13	14	2 028	CK-1/8-PK-6	10
G1/4	2.9	4	27.2	6	17	12	2 029	CK-1/4-PK-4	10
	4.9	6	27.3	6	17	14	2 030	CK-1/4-PK-6	10
	8	9	30.6	6	17	19	2 031	CK-1/4-PK-9	10
G3/8	4.9	6	28.3	7	19	14	2 032	CK-3/8-PK-6	10
	8	9	31.6	7	19	19	2 033	CK-3/8-PK-9	10
	11.7	13	33.2	7	24	24	4 097	CK-3/8-PK-13	10
G1/2	11.7	13	34.7	8.5	24	24	4 098	CK-1/2-PK-13	1
Polymer design									
G1/8	2.4	3	22.2	6.5	13	8	6 253	CK-1/8-PK-3-KU	10
	3.4	4	25.3	6.5	13	12	6 254	CK-1/8-PK-4-KU	10
	4.4	6	25.4	6.5	13	14	6 255	CK-1/8-PK-6-KU	10
G1/4	3.4	4	28.5	8.5	17	12	6 256	CK-1/4-PK-4-KU	10
	5.3	6	28.6	8.5	17	14	6 257	CK-1/4-PK-6-KU	10
	7.3	9	31.9	8.5	17	19	6 258	CK-1/4-PK-9-KU	10
G3/8	5.3	6	31	10.5	19	14	6 460	CK-3/8-PK-6-KU	10
	8	9	34.5	10.5	19	19	6 468	CK-3/8-PK-9-KU	10

* Packaging unit quantity


Bulkhead quick connectors QCK

Technical data



Bulkhead quick connector QCK
Female thread with sealing ring

Material:
Blue anodised aluminium/steel
Free of copper, PTFE and silicone



Dimensions and ordering data														
Connection	Nominal size	Tubing I.D.	B1	D5	L1	L2	L3	L4 max.	≲C1	≲C2	≲C3	Part No.	Type	PU*
D1	[mm]													
M5	2.4	3	3.2	M6x0.75	31	6	10	8	7	8	10	9 424	QCK-M5-PK-3-B	1
G1/8	3.4	4	3.5	M10x1	40	8	13.5	10	13	12	13	9 425	QCK-1/8-PK-4-B	1
G1/4	5.3	6	4	M12x1	45	12	18	10	17	14	17	9 426	QCK-1/4-PK-6-B	1
G3/8	8	9	5	M16x1	50	12	18.6	10	19	19	22	9 427	QCK-3/8-PK-9-B	1

* Packaging unit quantity

Bulkhead quick connectors SCK

Technical data

FESTO

Bulkhead quick connector SCK

Material:

Blue anodised aluminium/steel

Free of copper, PTFE and silicone

Bulkhead quick connector SCK-...-KU


Material:

Polymer with moulded-on sealing ring

Free of copper, PTFE and silicone

Pressure range: 0 ... 10 bar

Temperature range: -10 ... +60 °C



Dimensions and ordering data									
Nominal size	Tubing I.D.	B1	D5	L1	L2 max.	≡C1	Part No.	Type	PU*
[mm]									
Aluminium design									
2.4	3	3.2	M6x0.75	34	8	10	9 420	SCK-PK-3	1
3.4	4	3.5	M10x1	43	10	13	9 421	SCK-PK-4	1
5.3	6	4	M12x1	44	10	17	9 422	SCK-PK-6	1
8	9	5	M16x1	53	10	22	9 423	SCK-PK-9	1
Polymer design									
2.4	3	5	M10x1 ¹⁾	41	10	13	9 387	SCK-PK-3-KU	10
3.4	4	5	M10x1	46		13	9 388	SCK-PK-4-KU	10
5.3	6	6	M12x1	48		17	9 389	SCK-PK-6-KU	10
8	9	7	M16x1	57		22	9 390	SCK-PK-9-KU	1

* Packaging unit quantity

1) Installation diameter varies from aluminium version

End caps CV


Technical data

FESTO

End cap CV

for sealing barbed fittings and connectors for polymer tubing

Material:
Polyurethane



Dimensions and ordering data				
Tubing I.D.	Weight/piece [g]	Part No.	Type	PU*
3	0.001	6 213	CV-PK-3-B	10
4	0.001	6 214	CV-PK-4-B	10
6	0.001	6 215	CV-PK-6-B	10
9	0.002	6 216	CV-PK-9-B	10

Operating conditions (permissible static pressure)								
Type	CV-PK-3-B ... CV-PK-6-B						CV-PK-9-B	
Operating pressure [bar]	10	10	8	7	6	6	6	4
Ambient temperature [°C]	-35	+20	+40	+60	+80	+60	+60	+80

* Packaging unit quantity

Elbow quick connectors GCK

Technical data

FESTO

Elbow quick connector GCK-...-KU


Material:

Polymer

Free of copper, PTFE and silicone

Pressure range: 0 ... 10 bar

Temperature range: -10 ... +60 °C



Dimensions and ordering data												
Connection D1	Nominal size [mm]	Tubing I.D.	B1	H1	H2	H3	L1	L2	≅C1	Part No.	Type	PU*
R1/8	3	4	13	22.5	8	16.5	26.5	20.5	20.5	6 267	GCK-1/8-PK-4-KU	10
	4.5	6	17	24.5	8	17.5	28.5	21.5	21.5	6 268	GCK-1/8-PK-6-KU	10
R1/4	3	4	17	25.5	11	19.5	30	22.5	22.5	6 269	GCK-1/4-PK-4-KU	10
	4.5	6	17	27.5	11	20.5	30	22.5	22.5	6 270	GCK-1/4-PK-6-KU	10
R3/8	4.5	6	19	28.5	10.5	21	34	24.5	24.5	6 271	GCK-3/8-PK-6-KU	10
	7	9	19	33.5	10.5	23.5	37.2	27.7	27.7	6 272	GCK-3/8-PK-9-KU	10

* Packaging unit quantity

Elbow quick connectors LCK

Technical data

FESTO


Elbow quick connector LCK
rotatable with 2 sealing rings

Material:
Die-cast zinc
Free of copper, PTFE and silicone

Elbow quick connector
LCK-...-KU
rotatable with moulded-on sealing
ring

Material:
Polymer
Free of copper, PTFE and silicone

Pressure range: 0 ... 10 bar
Temperature range: -10 ... +60 °C



Dimensions and ordering data													
Connection	Nominal size	Tubing I.D.	B1	H1	H2	L1	L2	L3	≡C1	≡C2	Part No.	Type	PU*
D1	[mm]												
Die-cast zinc design													
M5	2	3	10	21.1	16.1	18.2	4.2	5.7	7	7	4 468	LCK-M5-PK-3	10
	2.9	4	11	21.1	16.1	18.2	3.4	5.7	7	7	4 562	LCK-M5-PK-4	10
G1/8	2	3	16	27.1	19.1	22	6.4	6	13	13	4 136	LCK-1/8-PK-3	10
	2.9	4	16	30.2	22.2	27.5	6	9	13	13	4 469	LCK-1/8-PK-4	10
	4.9	6	16	30.3	22.3	27.5	6	9	13	13	4 470	LCK-1/8-PK-6	10
G1/4	2.9	4	20	34.2	24.2	28.5	7	9	17	17	4 471	LCK-1/4-PK-4	10
	4.9	6	20	34.3	24.3	28.5	6.8	9.1	17	17	4 472	LCK-1/4-PK-6	10
	8	9	20	37.6	27.6	33.7	7.3	11.6	17	17	11 452	LCK-1/4-PK-9	10
G3/8	4.9	6	25	39.3	26.8	31	8.6	9.1	22	22	4 473	LCK-3/8-PK-6	1
	8	9	25	42.6	30.1	36.5	9.1	11.6	22	22	4 474	LCK-3/8-PK-9	1
G1/2	11.7	13	30	49.2	34.2	50	12.7	16.5	27	27	4 100	LCK-1/2-PK-13	1
Polymer design													
G1/8	3.4	4	16	30.5	22.5	27.5	7.1	8.25	13	13	6 259	LCK-1/8-PK-4-KU	10
	5.3	6	16	30.5	22.5	27.5	7.1	8.25	13	13	6 260	LCK-1/8-PK-6-KU	10
G1/4	3.4	4	20	34.5	24.5	28.5	8.1	8.25	17	17	6 261	LCK-1/4-PK-4-KU	10
	5.3	6	20	34.5	24.5	28.5	8.1	8.25	17	17	6 262	LCK-1/4-PK-6-KU	10

* Packaging unit quantity

Elbow quick connectors LCKN


Technical data

FESTO

Elbow quick connector LCKN
rotatable with sealing ring OL...

Material:
Die-cast zinc/aluminium with sealing
ring

Note: Cannot be used as a rotary
distributor.



Dimensions and ordering data												
Connection D1	Nominal size [mm]	Tubing I.D.	H1	H2	H3	L1	L2	≡G1	≡G2	Part No.	Type	PU*
M5	1.7	3	22.2	3.55	15.15	20.1	16.1	7	8	164 995	LCKN-M5-PK-3	10
	2.6	4	24.3	3.55	15.75	23.2	19.2	7	–	164 996	LCKN-M5-PK-4	10
G1/8	1.7	3	24.6	4.7	15.9	25.4	18.9	13	8	164 997	LCKN-1/8-PK-3	10
	2.6	4	27	4.7	16.3	28.5	22	13	12	164 998	LCKN-1/8-PK-4	10
	4.6	6	30.3	4.7	18.6	28.6	22.1	13	14	164 999	LCKN-1/8-PK-6	10
G1/4	2.6	4	29.5	5.8	17.7	28.5	22	17	12	165 000	LCKN-1/4-PK-4	10
	4.6	6	32.8	5.8	20.0	28.6	22.1	17	14	165 001	LCKN-1/4-PK-6	10
G3/8	4.6	6	33.8	6.0	20.8	28.6	22.1	19	14	165 002	LCKN-3/8-PK-6	1

* Packaging unit quantity

T quick connectors TCK


Technical data

FESTO

T quick connector TCK rotatable

Material:

Die-cast zinc with 2 sealing rings
Thread G $\frac{3}{8}$ and G $\frac{1}{2}$ aluminium, blue
anodised
Free of copper, PTFE and silicone



T quick connector

TCK-...-KU

rotatable

Material:

Polymer with moulded-on sealing ring
Free of copper, PTFE and silicone

Pressure range: 0 ... 10 bar

Temperature range: -10 ... +60 °C

Dimensions and ordering data												
Connection D1	Nominal size [mm]	Tubing I.D.	H1	H2	H3	L1	L2	1	2	Part No.	Type	PU*
Die-cast zinc design												
M5	2.4	3	18.2	4.2	5.7	21.1	10	7	8	4 484	TCK-M5-PK-3	10
	3.4	4	18.2	3.4	5.7	21.1	11	7	8	4 563	TCK-M5-PK-4	10
G $\frac{3}{8}$	2.4	3	22	6.4	6	38.2	16	13	8	4 137	TCK- $\frac{3}{8}$ -PK-3	10
	3.4	4	27.5	6	9	44.4	16	13	12	4 485	TCK- $\frac{3}{8}$ -PK-4	10
	5.3	6	27.5	6	9	44.6	16	13	14	4 486	TCK- $\frac{3}{8}$ -PK-6	10
G $\frac{1}{4}$	3.4	4	28.5	7	9	48.4	20	17	12	4 487	TCK- $\frac{1}{4}$ -PK-4	10
	5.3	6	28.5	6	9.1	48.6	20	17	14	4 488	TCK- $\frac{1}{4}$ -PK-6	10
Aluminium design												
G $\frac{3}{8}$	5.3	6	31	9	9	53.6	25	22	14	4 489	TCK- $\frac{3}{8}$ -PK-6	1
	8	9	36.5	9.1	11.7	60.2	25	22	14	4 490	TCK- $\frac{3}{8}$ -PK-9	1
G $\frac{1}{2}$	12	13	50	12.5	16.7	68.4	30	27	24	4 101	TCK- $\frac{1}{2}$ -PK-13	1
Polymer design												
G $\frac{3}{8}$	3.4	4	27.5	7.1	8.25	45	16	13	12	6 263	TCK- $\frac{3}{8}$ -PK-4-KU	10
	5.3	6	27.5	7.1	8.25	45	16	13	14	6 264	TCK- $\frac{3}{8}$ -PK-6-KU	10
G $\frac{1}{4}$	3.4	4	28.5	8.1	8.25	49	20	17	12	6 265	TCK- $\frac{1}{4}$ -PK-4-KU	10
	5.3	6	28.5	8.1	8.25	49	20	17	14	6 266	TCK- $\frac{1}{4}$ -PK-6-KU	10

* Packaging unit quantity

T quick connectors FCK

Technical data

FESTO

T-distributor FCK-...-KU


Material:

Polymer

Free of copper, PTFE and silicone

Pressure range: 0 ... 10 bar

Temperature range: -10 ... +60 °C



Dimensions and ordering data												
Tubing I.D.	Nominal size [mm]	B1	D5	H1	H2	H3	L1	L2	≅1	Part No.	Type	PU*
3	2.4	11	4.3	22.9	18.9	5	37.8	10	8	6 273	FCK-3-PK-3-KU	10
4	3.4	15	4.3	29	23	6	46	12	12	6 274	FCK-3-PK-4-KU	10
6	5.3	18	4.3	30.1	23.1	6	46.2	12	14	6 275	FCK-3-PK-6-KU	10
9	8	22	4.3	37	28.5	7.1	53.8	13	19	6 276	FCK-3-PK-9-KU	10

* Packaging unit quantity

Locknut MCK

Technical data

FESTO

Locknut MCK

for tube connectors

Material:


Blue anodised aluminium

Locknut MCK-...-KU

for tube connectors

Material:

Polymer design



Dimensions and ordering data						
Tubing I.D.	D1	L1	±0.1	Part No.	Type	PU*
Aluminium design						
3	M6x0.75	8.5	8	205 254	MCK-PK-3	1
4	M10x1	11	12	2 965	MCK-PK-4 ¹⁾	1
4	M8x1	9.5	–	205 257	MCK-PK-4-R ²⁾	1
6	M12x1	11	14	2 966	MCK-PK-6	1
9	M16x1	14.4	19	2 967	MCK-PK-9	1
13	M22x1	18	24	206 504	MCK-PK-13	1
Polymer design						
3	M6x0.75	9.5	8	211 289	MCK-PK-3-KU	1
4	M10x1	12.5	12	211 291	MCK-PK-4-KU ¹⁾	1
6	M12x1	12.5	14	211 292	MCK-PK-6-KU	1
9	M16x1	16	19	211 293	MCK-PK-9-KU	1

* Packaging unit quantity

1) except for connectors CK-M5-PK-4, LCK-M5-PK-4, TCK-M5-PK-4

2) for connectors CK-M5-PK-4, LCK-M5-PK-4, TCK-M5-PK-4

Multiple distributors

Technical data

FESTO


Hollow bolt VT with ring piece LK
(one outlet connection)

Materials:

Hollow bolt: Galvanised steel

Ring piece LK: Die-cast zinc

Ring piece LK-...-KU: Polymer



Ordering data				Dimensions → 3 / 5.5-18			
Hollow bolt				Ring piece			
Pneumatic connection	No. of ring pieces	Part No.	Type	Pneumatic connection	Part No.	Type	PU*
Die-cast zinc design							
M5	2	206 145	VT-M5-2	for 3 mm tubing	4 475	LK-M5-PK-3 ¹⁾	10
	3	4 594	VT-M5-3				
G1/8	2	4 593	VT-1/8-2-PK-3	for 3 mm tubing	4 597	LK-1/8-PK-3 ¹⁾	10
	3	4 595	VT-1/8-3-PK-3				
G1/8	2	206 146	VT-1/8-2	for 4 mm tubing	4 476	LK-1/8-PK-4 ¹⁾	10
	3	4 596	VT-1/8-3				
G1/8	2	206 146	VT-1/8-2	for 6 mm tubing	4 477	LK-1/8-PK-6 ¹⁾	10
	3	4 596	VT-1/8-3				
G1/4	2	206 147	VT-1/4-2	for 4 mm tubing	4 478	LK-1/4-PK-4 ¹⁾	10
	3	2 335	VT-1/4-3				
G1/4	2	206 147	VT-1/4-2	for 6 mm tubing	4 479	LK-1/4-PK-6 ¹⁾	10
	3	2 335	VT-1/4-3				
G3/8	2	206 148	VT-3/8-2	for 6 mm tubing	4 480	LK-3/8-PK-6 ¹⁾	1
	3	2 336	VT-3/8-3				
Polymer design							
G1/8	2	206 146	VT-1/8-2	for 4 mm tubing	6 280	LK-1/8-PK-4-KU ²⁾	10
	3	4 596	VT-1/8-3				
G1/8	2	206 146	VT-1/8-2	for 6 mm tubing	6 281	LK-1/8-PK-6-KU ²⁾	10
	3	4 596	VT-1/8-3				
G1/4	2	206 147	VT-1/4-2	for 4 mm tubing	6 282	LK-1/4-PK-4-KU ²⁾	10
	3	2 335	VT-1/4-3				
G1/4	2	206 147	VT-1/4-2	for 6 mm tubing	6 283	LK-1/4-PK-6-KU ²⁾	10
	3	2 335	VT-1/4-3				

* Packaging unit quantity

1) with 2 sealing rings

2) with moulded-on sealing ring, pressure range 0...10 bar, temperature range -10...+60 °C

Multiple distributors

Technical data

FESTO


Hollow bolt VT with ring piece TK (2 outlet connections)

Materials:

Hollow bolt: Galvanised steel

Ring piece TK: Die-cast zinc

Ring piece TK-...-KU: Polymer



Ordering data				Dimensions → 3 / 5.5-18		
Hollow bolt				Ring piece		
Pneumatic connection	No. of ring pieces	Part No.	Type	Pneumatic connection	Part No.	PU*
Die-cast zinc design						
M5	2	206 145	VT-M5-2	for 3 mm tubing	4 491	TK-M5-PK-3 ¹⁾
	3	4 594	VT-M5-3			
G ¹ / ₈	2	4 593	VT- ¹ / ₈ -2-PK-3	for 3 mm tubing	4 598	TK- ¹ / ₈ -PK-3 ¹⁾
	3	4 595	VT- ¹ / ₈ -3-PK-3			
	2	206 146	VT- ¹ / ₈ -2	for 4 mm tubing	4 492	TK- ¹ / ₈ -PK-4 ¹⁾
	3	4 596	VT- ¹ / ₈ -3			
	2	206 146	VT- ¹ / ₈ -2	for 6 mm tubing	4 493	TK- ¹ / ₈ -PK-6 ¹⁾
	3	4 596	VT- ¹ / ₈ -3			
G ¹ / ₄	2	206 147	VT- ¹ / ₄ -2	for 4 mm tubing	4 494	TK- ¹ / ₄ -PK-4 ¹⁾
	3	2 335	VT- ¹ / ₄ -3			
	2	206 147	VT- ¹ / ₄ -2	for 6 mm tubing	4 495	TK- ¹ / ₄ -PK-6 ¹⁾
	3	2 335	VT- ¹ / ₄ -3			
G ³ / ₈	2	206 148	VT- ³ / ₈ -2		4 496	TK- ³ / ₈ -PK-6 ¹⁾
Polymer design						
G ¹ / ₈	2	206 146	VT- ¹ / ₈ -2	for 4 mm tubing	6 284	TK- ¹ / ₈ -PK-4-KU ²⁾
	3	4 596	VT- ¹ / ₈ -3			
	2	206 146	VT- ¹ / ₈ -2	for 6 mm tubing	6 285	TK- ¹ / ₈ -PK-6-KU ²⁾
	3	4 596	VT- ¹ / ₈ -3			
G ¹ / ₄	2	206 147	VT- ¹ / ₄ -2	for 4 mm tubing	6 286	TK- ¹ / ₄ -PK-4-KU ²⁾
	3	2 335	VT- ¹ / ₄ -3			
	2	206 147	VT- ¹ / ₄ -2	for 6 mm tubing	6 287	TK- ¹ / ₄ -PK-6-KU ²⁾
	3	2 335	VT- ¹ / ₄ -3			

* Packaging unit quantity

1) with 2 sealing rings

2) with moulded-on sealing ring, pressure range 0...10 bar, temperature range -10...+60 °C

Multiple distributors

Technical data

FESTO


Multiple distributor

consisting of:

- Hollow bolt VT and ring piece LK
→ 3 / 5.5-16

or

- Hollow bolt VT and ring piece TK
→ 3 / 5.5-17



Dimensions													
Connection D1	Hollow bolt Type	Ring piece Type	H1	H2	H3	H4	H5	L1	L2	L3	≈C1	≈C2	
M5	VT-M5-2	LK-M5-PK-3	30	5.9	5.7	16.1	–	–	5	16.1	7	8	
		TK-M5-PK-3						32.2	–				
	VT-M5-3	LK-M5-PK-3	40	6.1	5.7	16.1	26.5	–	5	16.1	7	8	
		TK-M5-PK-3						32.2	–				
G1/8	VT-1/8-2-PK-3	LK-1/8-PK-3	32.5	6.9	6	16.5	–	–	8	19.1	13	8	
		TK-1/8-PK-3						38.2	–				
	VT-1/8-3-PK-3	LK-1/8-PK-3	43	7.3	6	16.5	27	–	8	19.1	13	8	
		TK-1/8-PK-3						38.2	–				
	VT-1/8-2	LK-1/8-PK-4	44	6.5	9	25.5	–	–	8	22.2	13	12	
		TK-1/8-PK-4						44.4	–				
		LK-1/8-PK-6						–	8	22.3		14	
		TK-1/8-PK-6						44.6	–				
	VT-1/8-3	LK-1/8-PK-4	60.5	6.5	9	25.5	42	–	8	22.2	13	12	
		TK-1/8-PK-4						44.4	–				
		LK-1/8-PK-6						–	8	22.3		14	
		TK-1/8-PK-6						44.6	–				
G1/4	VT-1/4-2	LK-1/4-PK-4	45	8	9	25	–	–	10	24.2	17	12	
		TK-1/4-PK-4						48.4	–				
		LK-1/4-PK-6		7.6	9.1	25.3		–	10	24.3		14	
		TK-1/4-PK-6						48.6	–				
	VT-1/4-3	LK-1/4-PK-4	62.5	8.8	9	25	41	–	10	24.2	17	12	
		TK-1/4-PK-4						48.4	–				
		LK-1/4-PK-6		8.2	9.1	25.3		41.5	–	10		24.3	14
		TK-1/4-PK-6							48.6	–			
G3/8	VT-3/8-2	LK-3/8-PK-6	48	9.6	9.1	25.3	41.5	–	12.5	26.8	22	14	
		TK-3/8-PK-6		10.4	9	25	41	53.6	–				
	VT-3/8-3	LK-3/8-PK-6	65	9.6	9.1	25.3	41.5	–	12.5	26.8	22	14	
		TK-3/8-PK-6		10.4	9	25	41	53.6	–				

Quick connectors ACX/CX, metal braided hose

FESTO


Technical data

Quick connector ACX

Female thread with sealing ring for metal braided hose PX

Material:

Anodised aluminium



Dimensions and ordering data									
Connection D1	Nominal size [mm]	Tubing I.D.	L1	L2	≡C1	≡C2	Part No.	Type	PU*
G $\frac{1}{8}$	3.5	4	35	10	13	12	4 032	ACX- $\frac{1}{8}$ -PX-4	1
G $\frac{1}{4}$	5	6	43	12	17	14	4 033	ACX- $\frac{1}{4}$ -PX-6	1
G $\frac{3}{8}$	8	9	54	15	22	19	4 034	ACX- $\frac{3}{8}$ -PX-9	1


* Packaging unit quantity

Quick connector CX

Male thread with sealing ring for metal braided hose PX

Material:

Anodised aluminium



Dimensions and ordering data									
Connection D1	Nominal size [mm]	Tubing I.D.	L1	L2	≡C1	≡C2	Part No.	Type	PU*
G $\frac{1}{8}$	3.5	4	31.5	5	13	12	4 035	CX- $\frac{1}{8}$ -PX-4	10
	5	6	36.5	5	13	14	4 453	CX- $\frac{1}{8}$ -PX-6	10
G $\frac{1}{4}$	3.5	4	34	6	17	12	4 454	CX- $\frac{1}{4}$ -PX-4	10
	5	6	39	6	17	14	4 036	CX- $\frac{1}{4}$ -PX-6	10
G $\frac{3}{8}$	8	9	47	7	22	19	4 037	CX- $\frac{3}{8}$ -PX-9	1

* Packaging unit quantity

Quick connectors LCX/TCX, metal braided hose

Technical data


FESTO

Elbow quick connector LCX

rotatable with 2 sealing rings for metal braided hose PX

Material:

Anodised aluminium



Dimensions and ordering data

Connection D1	Nominal size [mm]	Tubing I.D.	B1	L1	L2	L3	H1	H2	≈C1	≈C2	Part No.	Type	PU*
G1/8	3.5	4	16	27.5	5.3	9.1	39.5	31.5	13	12	4 041	LCX-1/8-PX-4	1
G1/4	5	6	20	35	6.8	11.6	46	36	17	14	4 042	LCX-1/4-PX-6	1
G3/8	8	9	25	43.5	9.3	14.1	58	45.5	22	19	4 043	LCX-3/8-PX-9	1


* Packaging unit quantity

T quick connector TCX

rotatable with 2 sealing rings for metal braided hose PX

Material:

Anodised aluminium



Dimensions and ordering data

Connection D1	Nominal size [mm]	Tubing I.D.	H1	H2	H3	L1	L2	≈C1	≈C2	Part No.	Type	PU*
G1/8	3.5	4	27.5	5.3	9.1	63	16	13	12	4 044	TCX-1/8-PX-4	1
G1/4	5	6	35	6.8	11.6	72	20	17	14	4 045	TCX-1/4-PX-6	1
G3/8	8	9	43.5	9.3	14.1	91	25	22	14	4 046	TCX-3/8-PX-9	1

* Packaging unit quantity