

Cuplaj
EAMC-65-90-XX-25
Numar piesa: 176038

FESTO



Fisa de date

Caracteristica	Valoare
Diametru de montare 2	25 mm
Dimensiune	65
Lungime nominala	90 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	417 kgmm ²
Greutate produs	535 g
Nota privind materialele	Conform RoHS